


HR2LEDT309P

2" Tesla™ Pro LED 0°-30° Adjustable Trim

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project:

Location:

PRODUCT DESCRIPTION

Minimum profile, round 0° to 30° adjustable trim with interior open reflector.

FEATURES

- 2" aperture
- Damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 5 year WAC Lighting product warranty

SPECIFICATIONS

Construction: Durable die-cast aluminum construction with borosilicate glass lens. Extruded aluminum heat sink.

Light Source: Utilizes one 14.5W LED, CRI: 85 & 90+

Dimming: 0-10V Dimming: 100%-10%
ELV Dimming: 100%-15% (120V only)

Mounting: Two heavy gauge retention clips hold trim firmly to housing

Finish: White (WT) powder coat paint and electroplated Brushed Nickel (BN) and Copper Bronze (CB).

Standards: ETL & cETL Listed.

TRIMS

Model#	Beam	Color Temp	CRI	Lumens	CBCP	Finish
HR2LEDT309P 0°-30° Adjustable	N 27°	827 2700K	85	780	2020	BN Brushed Nickel CB Copper Bronze WT White
		927 2700K	90	635	1619	
		830 3000K	85	810	2044	
		930 3000K	90	730	1924	
		835 3500K	85	875	2227	
	840 4000K	85	895	2332		
	F 40°	827 2700K	85	750	1315	
		927 2700K	90	610	1038	
		830 3000K	85	785	1371	
		930 3000K	90	695	1181	
		835 3500K	85	840	1458	
	840 4000K	85	865	1507		

HR2LEDT309P

Example: HR2LEDT309PF835BN

COMPATIBLE HOUSINGS See individual housing spec sheets for complete information.

REPLACEMENT MODULES

New Construction

HR-2LED-H09D-ICA IC-Rated, Airtight 120V-277V	HR-2LED-H09D-ICAC IC-Rated, Airtight Chicago Plenum 120V-277V
--	---

Reflectors

Narrow Flood	SL-REF-BL10-1-N
Flood	SL-REF-BL10-1-F

Remodel

HR-2LED-R14D Non-IC 120V-277V
--

LED

2700K (90 CRI)	BXRC-27G1000-B-23
2700K	BXRC-27E1000-B-23
3000K (90 CRI)	BXRC-30G1000-B-23
3000K	BXRC-30E1000-B-23
3500K	BXRC-35E1000-B-23
4000K	BXRC-40E1000-B-23

wacighting.com
Phone (800) 526.2588
Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive
Port Washington, NY 11050

Central Distribution Center
1600 Distribution Ct
Lithia Springs, GA 30122

Western Distribution Center
1750 Archibald Avenue
Ontario, CA 91760