

Ridley II Collection  
 52 Inch Ridley II Fan OBB  
 300027OBB (Oil Brushed Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_



### Product Information

Product ID	300027OBB
Finish	Oil Brushed Bronze
Blade Finish	Walnut
Collection	Ridley II Collection

### Specifications

Number of Blades	3
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	No
Blade Material	SOLID WOOD
Optional Blades Available	No
Downrod 1	1.00 OD X 4.50
Primary Control System	3 Speed Wall Control Basic
Remote Included	No
Wall Control Included	Yes
Low Ceiling Adaptable	No
Lead Wire Length	78.00"
Motor Size	153MM X 18MM
Motor Type	AC INDUCTION

### Dimensions



Downrod	A	B	C	D
1.00 OD X 4.50	16.25	13.25	6.75	5.75

### Downlight

Downlight Included	Yes
Light Source	LED
Downlight Bulb Included	Integrated
Downlight Bulb Type	LED
# of Bulbs/LED Modules	1
Watts	17 W
Initial Lumens	1600
Glass Description	Etched Cased Opal
Optional Light Kit Available	No
Efficacy (LMIW)	94
Kelvin Temperature	3000 K
Color Rendering Index	80

### Available Finishes

Finish	Fixture	Glass	Blade 1	Blade 2

### Safety Listings & Certifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

### Installation

The electrical junction box

**Ridley II Collection**  
**52 Inch Ridley II Fan OBB**  
 300027OBB (Oil Brushed Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

Brushed Stainless Steel	300027BSS	ETCHED CASED OPAL	MEDIUM OAK	
Natural Brass	300027NBR	ETCHED CASED OPAL	CHERRY	
Oil Brushed Bronze	300027OBB	ETCHED CASED OPAL	WALNUT	

Installation requirements	and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""
Electrical Requirements	120V 60Hz AC
Hanging Weight	17.20 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7 feet