

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3716-09

Bound Beveled Glass

Six-sided foyer fixture with clear, bound beveled glass in a brushed nickel finish. Solid brass construction. Perfect for entry ways.

Category: Hall & Foyer

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Clear beveled glass panels



Diameter: 13"
Height: 20"
Overall ht. w/chain: 47"

Glass: 6-1/4"
Height: 8-7/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 24" 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5" dia., 1"	Pre-wired 156" of wire supplied 120V	Quantity: 3 60W Candelabra Base Candelabra sockets	UL-CUL Damp location listed 1 year warranty Companion Close-to-ceiling, Hall and Foyer, Pendant, Post top lantern, Wall lantern fixtures are available