


LED Undercabinet Fixture

DIMENSIONS



APPLICATION

The UCL series is a next generation, direct wire undercabinet fixture that Provides task or accent lighting in commercial, retail, hospitality and residential applications. Ideal for use under and over cabinets, display cases, task lighting, office lighting, coves and utility/work areas. Standard knockouts are located on top, back or ends for direct connection. A direct wire UL listed connector is included and is suitable for 3/8" flexible conduit or 3 wire Romex.

FEATURES

- High-transmission (White) Acrylic lens with excellent distribution and uniformity.
- Direct replacement for fluorescent
- 120V line voltage fixture
- Low profile (1" deep)
- Hard-wire connections
- Four finishes available (white, black, nickel and oil-rubbed bronze)
- Optional Rocker switch
- Hinged Wireway cover
- Option for 3000/4000 Kelvin, Duel Kelvin switching

QUICK SHIP

- UCL-9-5-120D-930/40-WH
- UCL-12-5-120D-930/40-WH
- UCL-18-9-120D-930/40-WH
- UCL-21-9-120D-930/40-WH
- UCL-24-9-120D-930/40-WH
- UCL-33-14-120D-930/40-WH
- UCL-42-18-120D-930/40-WH

CONSTRUCTION

Low profile steel housing available in white, nickel, satin, or oil rubbed bronze finishes. Designed to prevent "hot spots" on counter tops. Lens design and materials provide uniform appearance without pixilation.

MOUNTING

Designed for mounting on 3" electrical using J-Box.

ELECTRICAL

Equipped standard with 120V 15-100% triac dimming driver operating at 60Hz.

CERTIFICATION

All luminaires are built to UL 1598 and 2108 standards, and bear appropriate ETL labels. Wet location labeling is standard. Emergency equipped fixtures labeled UL924. Adheres to LM70, LM80, and TM21 industry standards. Dedicated 120V Models are FCC Title 47 CFR, Part 15, Class B for residential and commercial applications. California Title 24 Compliant, JA8 compliant, CEC listed.

WARRANTY

3-year limited warranty. See complete warranty for terms and exclusions. (Labor not included).

ORDERING INFORMATION

Example Model Number: UCL-12-4-120D-930-WH

SERIES	FORM FACTOR	RATED WATTAGE	DRIVER TYPE	CRI AND KELVIN	FINISH
UCL	9-9" Length 12- 12" Length ² 18- 18" Length ² 24- 24" Length ² 33- 33" Length ² 42- 42" Length ²	5-5W, 9" Length ² 5- 5W, 12" Length ² 9-9W, "18" Length ² 9-9W, "21" Length ² 9- 9W, 24" Length ² 14-14W, 33" Length ² 18-18W, 42" Length ²	120D- 120V, Triac Dimming ² MV- 120-277V ¹	930/40-90 CRI; 3000-4000 Kelvin Dual color switch ² 930-90 CRI; 3000 Kelvin ¹ 940-90 CRI; 4000 Kelvin ¹	NS- Nickel Satin ^{1 2} ORB- Oil Rubbed Bronze ^{1 2} WH- White ²

Notes:

¹Made to order items. Minimum 90 day lead time. Minimum 500 order quantity.

²DLC Premium Listed

³Quick ship: 3000K. Other CCTs may require a lead time or be a special order.

⁴Typical color consistency, may vary or be changed.

⁵L70 hours calculated based on LED package manufacturer LM80 report and ISTMT report of LED in luminaire