

GENERATION LIGHTING

41161-962: Two Light Wall / Bath



Dimensions:

Width: 12 1/2" **Extends:** 5 1/2"
Height: 8 1/2" **Wire:** 6 1/2" (color/Black/White)
Weight: 3.3 lbs. **Mounting Proc.:** Cap Nuts
Connection: Mounted To Box

Bulbs:

2 - Medium A19 100w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1899FS)

Collection: Oslo

UPC #: 785652002984

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cased Opal Etched	2				5 29/32	3 15/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	4 3/4	8	13/16		6 1/4	2 1/4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	41161-962	1	785652002984	14.75	11.75	6.5	0.652	4.1	125	Yes
NJ Pallet		100		48	40	77	85.556	410		No
NV Pallet		110		48	40	77	85.556	451		No