



DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P5511-31

## Cast Aluminum

Wall fixture with threaded opal glass shades that screw onto fitter. Vapor-proof gaskets and porcelain sockets.

Category: Outdoor

Finish: Black (powdercoat)

Construction: Cast aluminum construction

Glass: White opal glass cylindrical diffuser



Width: 4-1/2"

Height: 7"

Depth: 5-7/8"

H/CTR: 3-1/4"

Glass: 3-3/4" dia.

Height: 6-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium porcelain socket	UL-CUL Wet location listed 1 year warranty Companion fixtures are available