




CATALOG NUMBERS:	04112
DESCRIPTION:	Tri-Source® STW three receptacle adapter cord set
APPROVALS:	UL Listed Adapter Cord Set, CSA Certified
CONSTRUCTION PARAMETERS:	
Conductor:	12AWG, 65/30 BC stranding
Jacket material:	PVC, orange
Overall cable O.D. (nom):	0.585 in
Cord rating:	Extra Hard Usage per the National Electric Code
Cord length:	2 ft
Attachment plug configuration:	NEMA 5-15P
Cord connector configuration:	NEMA 5-15R x 3
Plug and connector material:	PVC, orange
	
ELECTRICAL PROPERTIES:	
Cable temperature rating:	-20 to +60 °C
Maximum operating voltage:	125 VAC
Maximum operating current:	15 A
MARKINGS:	
Cable legend type:	Indent print
Logo/legend on fittings:	"E53440", Coleman Cable logo

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.

CUSTOMER APPROVAL:	Approved by: _____	Date: _____
	Title: _____	