



Electrical Utility

[Products](#) | [Solutions](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Rubber Tapes - Insulating and Splicing](#) > 3M™ Linerless Electrical Rubber Tape 2242, 2 in x 15 ft (51 mm x 4,6 m), 8 per case

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Linerless Electrical Rubber Tape 2242, 2 in x 15 ft (51 mm x 4,6 m), 8 per case

3M ID 80610973390 UPC# 00054007432517 Part Number 2242-2X15FT

[Print](#)

3M™ Linerless Splicing Compound 2242 is a highly conformable, linerless Ethylene Propylene Rubber-based tape.



Need Help? [ire](#)

Questions? We can help
[Contact Us](#)



Overview

Documents

3M™ Linerless Electrical Rubber Tape 2242 is used for all-voltage splicing, jacketing, & general insulating.

Specifications

Adhesive Material	Rubber Resin
Agency Approvals	ASTM D-4388 type 1, 2 & 3 HH-I-553C, HH-I-553C, ASTM D-4388 Type 1, 2 & 3
Backing Material	Rubber
Breaking Strength	7.5 lb/in
Color	Black
Dielectric Strength (V/mil)	750 V/mil
Emergency Overload Temperature (Celsius)	130 Degree Celsius
Emergency Overload Temperature (Fahrenheit)	266 Degree Fahrenheit
Family	3M™ Linerless Splicing Compound 2242
Length	15 Linear Foot
Material	Self-fusing Ethylene Propylene Rubber (EPR)
Operating Temperature (Celsius)	90 Degree Celsius
Operating Temperature (Fahrenheit)	194 Degree Fahrenheit
Product Family	3M™ Linerless Splicing Compound 2242
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls per Carton	1
Rolls per Case	8

Tape Grade	Premium
Tape Type	Rubber Insulating and Splicing
Tensile Strength	250 Pound-Force Per Square Inch
Tensile Strength lb/in (N/100 mm)	7.5 (131)
Thickness	30 mil
Trademark	Scotch
Width	2 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M Electrical Utility: [Contact Us](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.