




PRODUCT SPECIFICATION

GENERAL INFORMATION:

Catalog number: See table below
Description: 6/2 & 8/2 SRDT, 125/250V 50A range power supply cord kit with flanged spade terminals and metal strain relief
Approvals: UL Listed

CONSTRUCTION PARAMETERS:

Cable type: SRDT, round jacketed, black
Insulation and jacket material: PVC
Conductors: (2) 6 AWG & (2) 8 AWG, bare copper
Conductor color code: Black Red (6 ga), White Green (8 ga)
Overall cable O.D. (nom): 0.800"
Temperature rating: -20 to +60 deg C



Note: Plug style may vary

Plug configuration: NEMA 14-50P
Plug electrical ratings: 125/250 VAC, 50A
Plug material: PVC, black
Terminals: 1/4" flanged spade
Strain relief: Metal, included but not attached

CATALOG NUMBERS:

Length	Catalog number
4 ft	09044
5 ft	09045
6 ft	09046

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without the written consent of Coleman Cable Inc.