

# HANDY STRAPS®


	CAT. No.	MAXIMUM CABLE SIZE	NAIL/SCREW	PACKAGE AND QUANTITY	STD. CARTON QUANTITY	APPROX. SHIPPING Wt. PER CARTON
	CC-1005	12 AWG Ground Wire (.140" Dia.)	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
	CC-1010	RG59 (.242" Dia.)	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
	CC-1012	RG59 (.242" Dia.)	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
	CC-1016	RG59 (.242" Dia.)	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.
	CC-2010	RG59 Dual (.250" x .500")	1" x .080 Dia. Hardened Nail	Box of 100	1000	5 lbs.
	CC-1020	RG6 (.275" Dia.)	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
	CC-1022	RG6 (.275" Dia.)	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
	CC-1026	RG6 (.275" Dia.)	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.
	CC-2020	RG6 Dual (.305" x .594")	1" x .080 Dia. Hardened Nail	Box of 100	1000	5 lbs.
	CC-2022	RG6 Dual (.305" x .594")	#6 x 1" Phillips Head Self-Tapping Screw	Box of 50	500	5 lbs.
	CC-2026	RG6 Dual (.305" x .594")	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 50	500	5 lbs.
	CC-1030	RG6 Quad Shield (.300" Dia.)	1" x .080 Dia. Hardened Nail	Box of 100	1000	4 lbs.
	CC-1032	RG6 Quad Shield (.300" Dia.)	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
	CC-1036	RG6 Quad Shield (.300" Dia.)	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.
	CC-1060	RG11 (.395" Dia.)	1 3/16" x .080 Dia. Hardened Nail	Box of 100	1000	6 lbs.
	CC-1062	RG11 (.395" Dia.)	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
	CC-1066	RG11 (.395" Dia.)	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.

**Sturgeon Bay  
Metal Products, Inc.**

1018 Green Bay Road  
Sturgeon Bay, WI 54235-3815  
920-743-2221 or 800-423-7402  
Fax: 920-743-6190

# HANDY STRAPS®

We have expanded our line of the safest, most durable, time-saving fasteners for coaxial cable.



Sturgeon Bay Metal Products developed and patented a 2-nail metal strap for securing nonmetallic-sheathed cable (Romex) over 50 years ago. That revolutionary product has evolved into our complete line of plastic HANDY STRAPS for electrical wiring and coaxial cable.

Our fully insulated plastic straps prevent cable damage and ensure safe installation of coaxial cable. The heavy-duty plastic saddles are molded from a super-high impact plastic that will not break, even when used in cold temperatures.

The straps are black in color and UV stabilized for extended outdoor use. White, ivory, tan, and gray colored straps are available on special order.

We make our nails from high carbon wire, and they are heat treated for use in mortar joints or 'soft' masonry. Zinc plating and a new yellow chromate provide improved corrosion protection.

To prevent cable damage from an accidental hammer blow, we've introduced straps with a self-tapping screw (instead of a nail). The hardened #6 x 1" Phillips Head Self-Tapping Screw has a deeper #7 head for extra engagement with a power screwdriver. If used with a plastic screw anchor, these straps can be used on masonry.

For the toughest jobs, we've also introduced straps with a #8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw. The screw will cut threads in a pre-drilled hole in concrete, block, or any masonry material. This screw also works well in wood and light metal.

The standard black zinc plating on the screws provides exceptional corrosion resistance. If straps are ordered in any of the optional colors, screws with zinc plating and yellow chromate are used.

**Sturgeon Bay  
Metal Products, Inc.**