



Electrical Utility

[Products](#) | [Solutions](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Special Use Tapes](#) > 3M™ Temflex™ Cotton Friction Tape 1755, 1 1/2 in x 82 1/2 ft, Black

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Temflex™ Cotton Friction Tape 1755, 1 1/2 in x 82 1/2 ft, Black

3M ID 80610731715 UPC# 00054007502173 Part Number 1755-1-1/2X82-1/2FT

[Print](#)

3M™ Temflex™ Cotton Friction Tape 1755 is a high-grade, black friction tape designed to provide mechanical protection against abrasion and cut-through for cable, wire splices and connections insulated with rubber electrical tape.

- 1 1/2 in x 82 1/2 ft, Black
- High-grade, 13-mil friction tape
- Mechanical protection against abrasion and cut-through for cable, wire splices and connections insulated with rubber electrical tape
- Composed of a high-quality cotton fabric, coated on both sides with an electrical-grade, solvent-free, rubber adhesive
- High break strength and low stretch
- Ideal as a heavy-duty binding and harnessing tape



Need Help? [ire](#)

Questions? We can help [Contact Us](#)

Overview

Documents

The 13-mil thick tape is composed of a high-quality cotton fabric, coated on both sides with an electrical-grade, solvent-free, rubber adhesive. Tape has high break strength and low stretch, making it ideal as a heavy-duty binding and harnessing tape.

Specifications

Adhesive_Material	Thermosetable rubber resin
Backing_Material	Cotton Cloth
Breaking_Strength	48 lb/in
Color	Black
Family	3M™ Temflex™ Cotton Friction Tape 1755
Length	82.5 Linear Foot
Length_metric	25.1 m
Operating_Temperature_Range_Celsius	-10 to 80 Degree Celsius
Operating_Temperature_Range_Fahrenheit	15 to 176 Degree Fahrenheit
Product_Family	3M™ Temflex™ Cotton Friction Tape 1755
RoHS_2011_65_EU_Compliant	Yes
RoHS_EU_Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls_per_Carton	1
Rolls_per_Case	30
Tape_Grade	General Use
Tape_Type	Special Use
Tensile_Strength_lb_in_N_100_mm	48 (140)
Thickness	13 mil
Thickness_metric	0.33 mm
Trademark	Temflex
Width	1.5 Inch
Width_metric	38.1 mm

3M Electrical Utility: [Contact Us](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.