



S9866

3.5CTC/LED/CL/50K/120V
 3.5 watt CTC LED; Clear; Candelabra base; 5000K; 350 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S9866

This item has been discontinued.
 Possible replacement:

- [S29866](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9866	045923098666	120	3.5	40W	C11	Candelabra	E12

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
3.5CTC/LED/CL/50K/120V	Dimmable	Compatible dimmers for S9866	Clear	4-5/16"	1-3/8"	350	15000

Kelvin Temp	Color	CRI	Package Type	CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed
5000	Natural Light	80	Box	Non-Compliant Possible sub: S9877	Yes	Enclosed Rated	Yes

UL Classification	Warranty	Status	Suggested Substitute
cULus - Damp Location Rated	3 Year Limited	Discontinued	S29866



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

