


SIEMENS LOW VOLTAGE METER LOAD CENTER COMBINATION. FACTORY INSTALLED MAIN BREAKER 10 (1 INCH) SPACES INTERIOR ALLOWING MAX 20 CIRCUITS. 4-JAW METER / 1-PHASE SYSTEM RATED 100A. SPECIAL FEATURES: OH/UG FEED, RING TYPE COVER, FLUSH MOUNTING



Cable entry type	OH
Mounting type	Flush
Number of openings	10
<b>Electricity</b>	
Ampacity	100 A
Supply voltage frequency rated value 50/60 Hz	No
<b>Model</b>	
Product brand name	Siemens
Product sub brand name	Meter Combos
<b>Mechanical Design</b>	
Design of the terminal strip	Tin-plated aluminum extrusions 6061-T6
<b>General product approval</b>	
Certificate of suitability	EUSERC/UL67
<b>last modified:</b>	03/12/2018