



### 75061-782: Three Light Semi-Flush Mount



#### Dimensions:

**Diameter:** 15 3/4"      **Wire:** 6 1/2"  
**Height:** 12 1/2"      **Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box

#### Bulbs:

3 - Medium A19 100w Max. 120v - Not included

#### Features:

- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

#### Material List:

1 Body - Steel - Heirloom Bronze

#### Safety Listing:

Safety Listed for Dry Locations  
 Safety Listed for Dry Locations

#### Instruction Sheets:

English (HC-344)

**Collection:** Sussex

Sussex Three Light Close to Ceiling in Heirloom Bronze Finish with Satin Etched Glass.

The look that satisfies discerning taste. Part of our Sussex collection where past elements of design keep pace with today.

Design #: D20067

UPC #:785652750632

Finish: Heirloom Bronze (782)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1				5 11/16	15 3/4	13/32			

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			3	6 3/4		

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75061-782	1	785652750632	18.75	18.75	9.58	1.949	8.55	150	Yes
NJ Pallet		30		48	40	71.5	79.444	255		No
NV Pallet		30		48	40	71.5	79.444	255		No