



82029-12: One Light Outdoor Post Lantern



Collection: Kent

One Light Outdoor Post Lantern in Black Finish with Clear Beveled Glass

Outdoor post lantern finished black over die-cast aluminum with clear beveled glass. Fits 3" post (sold separately).

Design #: D20035

UPC #:785652820298

Finish: Black (12)

Dimensions:

Length: 8 3/8" **Wire:** 6 1/2"
Width: 8 3/8" **Bulb Appearance:** Clear
Height: 20 1/4"
Weight: 6.2 lbs.

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Die Cast Aluminum - Black

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-841)
 French (F-013)
 Trilingual (English, Spanish, and French) (990OP82_29-KEN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	4									
Panel	Glass	Clear Beveled	4									

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	82029-12	1	785652820298	11.25	11.25	22	1.611	7.8	150	Yes
NJ Pallet		56		48	40	75	83.333	436.8		No
NV Pallet		36		48	40	71	78.889	281		No