



Ocal[®]

Conduit Fittings-PVC Coated
T&B Catalog Number:

UPC Number: SS11/4-G
 70450840493
Status: Active
Description:

PVC Coated Strut Pipe Strap, Pipe Size 1-1/4 Inch/35 Metric, Use With Either 1-5/8 Inch or 1-1/2 Inch Strut, Steel, Gray

Features

Combination slot and hex head bolt for flexibility of attachment

Application

Designed for easy attachment of conduit to strut

General

Trade Size (inches)	1 1/4
Material	Steel
Finish	PVC Coated
Color	Gray

Dimension Information

Size (inches)	1 1/4
---------------	-------

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	27.5 lbs. per 100

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Dimensions are of uncoated fittings

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com