



Conduit Fittings-PVC Coated
T&B Catalog Number:

UPC Number: ST11/290-G
Status: 70450840639
Description: Active

PVC Coated Liquidtight Conduit Connector, 90 Degree, Pipe Size 1-1/2 Inch/41 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Dark Gray

Features

- A minimum of .040 in. (40 mil) PVC coating is bonded to the exterior.
- Double coated with a nominal .002 in. (2 mil) blue urethane on both the interior and exterior, before PVC coating is applied.
- Pressure-sealing sleeves are designed to protect the connection.
- PVC coated connectors are available in straight, 45 degree and 90 degree configurations
- Ocal uses T&B Industrial Liquidtight fittings to insure quality installations.

Application

To positively bond conduit to box or enclosure

General

Custom_Finish	It_112_90
Trade Size (inches)	1 1/2
Material	Steel
Finish	PVC Coated
Color	Dark Gray

Dimension Information

Pipe Size (Metric Size Designator*)	41
Dimension A (inches)	2 23/32
Dimension B (inches)	2 15/16
Dimension C (inches)	13/16

Technical Information

Chemical Resistance Chart Available on Website

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	1.7 lbs. Each

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Dimensional values are of uncoated liquidtight fittings.

Metric size designator (ANSI C80. 1-1994)

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com