

# Horizon 3000K LED Downlight White

43855WHLED30T (White)



Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

### Certifications / Qualifications

Commercial Grade	Yes
------------------	-----

### Certifications/Qualifications

ADA Compliant	Yes
Energy Star	Yes
Location Rating	Wet
Title 24 Compliant	Yes
<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>	

### Dimensions

Base Backplate	6.50 DIA
Weight	0.60 LBS
Height from center of Wall opening (Spec Sheet)	3.25"
Height	1.25"
Width	6.50"

### Electrical

Input Voltage	Single(120)V
---------------	--------------

### Mounting/Installation

Mountable on Wall or Ceiling	Yes
Interior/Exterior	Interior
Mounting Weight	0.60 LBS

### Photometrics

Color Rendering Index	90
Delivered Efficacy (Lumens/Watt)	68
Delivered Lumens	850
Kelvin Temperature	3000K

### Primary Lamping

Dimmable	Yes
Dimmable Notes	This LED is compatible with most standard incandescent dimmers, LED dimmers, and electronic low voltage dimmers. For more information, go to <a href="http://Kichler.com/dimming">Kichler.com\dimming</a>
Equivalent Light Source	Incandescent
Expected Life Span	40000
Lamp Included	Integrated
Light Source	LED
Max or Nominal Watt	12.5W
# of Bulbs/LED Modules	1


### Product/Ordering Information

SKU	43855WHLED30T
Finish	White
Style	Transitional
UPC	783927536721

### Specifications

Diffuser Description	Polycarbonate
Material	ALUMINUM

### Additional Finishes



White

---

**Kichler**

7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010  
Toll free: 866.558.5706 or kichler.com

**Notes:**

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

**KICHLER®**