



8882-08: One Light Outdoor Wall Lantern



Dimensions:

Width:	7"	Extends:	8"
Height:	17"	Wire:	6 1/2"
Mounting Proc.: Cap Nuts			
Connection: Mounted To Box			
Bulb Appearance: Clear			

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: Jamestowne

One Light Outdoor Wall Lantern in Textured Rust Patina with Clear Seeded Glass.

A warm and natural finish of textured rust patina over solid brass and clear seeded glass delivers timeless charm.

UPC #:785652888281

Finish: Textured Rust Patina (08)

Material List:

- 1 Body - Aluminum - Textured Rust Patina
- 1 Canopy - Aluminum - Textured Rust Patina
- 1 Bracket - Aluminum - Textured Rust Patina
- 1 Candle Cup - Aluminum - Textured Rust Patina

Safety Listing:

- Safety Listed for Wet Locations
- Safety Listed for Wet Locations

Instruction Sheets:

- English (HC-231)
- French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Seeded	4			5 7/16	8 9/16					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 1/2	4 3/4	3/4		6 1/2	10 1/2

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8882-08	1	785652888281	9	8.5	18.25	0.808	5.25	125	Yes
Master Pack		2	10785652888288	9	17	18.25	1.616	10.5	125	Yes
NJ Pallet		68		48	40	72	80	357		No
NV Pallet		80		48	40	72	80	420		No