

## F3191/4WOW/AF: 4 - Light Chandelier



### Dimensions:

<b>Length:</b>	18"	<b>Overall Height:</b>	84 1/4"
<b>Width:</b>	18"	<b>Wire:</b>	180" (color/Black)
<b>Height:</b>	26 3/4"	<b>Mounting Proc.:</b>	Center Lock-Up
<b>Weight:</b>	9.2 lbs.	<b>Connection:</b>	Mounted To Box

### Bulbs:

4 - Candelabra B10 Torpedo 60w Max. 120v - Not included

### Features:

•

### Material List:

- 1 Body - Steel - Antique Forged Iron
- 1 Cage - Steel - Weathered Oak Wood
- 4 12" Stem - Steel - Antique Forged Iron
- 1 6" Stem - Steel - Antique Forged Iron

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (F3191-4-F3192-6)

### Collection: Gannet

The Gannet lighting Collection by Feiss exudes rustic charm with a carefully crafted two-toned finish of painted, distressed Weathered Oak on an Antique Forged Iron metal frame. Clean, crisp edges and bold lines give a tailored look to this classic lantern silhouette. Gannet features open, airy frames on the sides and crown. The transitional lanterns of the Gannet Collection are offered in a 36"H x 25.5"W 6-light foyer chandelier, a 26.75"H x 18"W 4-light chandelier, a 17"H x 12"W 4-light chandelier, a dramatic 14"H x 50"L x 14"W 5-light linear island chandelier and a 12.5"H x 8.5"W 2-light wall sconce.

UPC #:014817574111

Finish: Weathered Oak Wood / Antique Forged Iron (WOW/AF)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/8			5		

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3191/4WOW/AF	1	014817574111	24.5	19.75	19.25	5.39	19.1	250	Yes
NJ Pallet		12		48	40	63	70	229.2		No
NV Pallet		12		48	40	63	70	229.2		No