

# CRAFTMADE

## Ricasso - RIC60BNK

60" Ceiling Fan (Blades Sold Separately)

**Finish:** Brushed Polished Nickel



Streamlined and symmetrical, this four-blade fan with LED lighting will give your room balance and panache. With its curved profile and polished finish, the Ricasso brings all the dramatic elements of the Art Deco period into a new era.

- Energy Saving, 6-Speed Reversible DC Motor
  - 6" Downrod (Included)
  - Blades Sold Separately
  - Integrated LED Light Source (Dimmable)
  - Remote & Wall Control Included
  - Dual Mount (Flat or Angled Ceiling)
  - LED Module is Guaranteed for 3 years
  - Optional Blank Light Lens Cover (Included)
  - Choice of 2 or 4 blade assembly. Choice of LED integrated lighting or blank off for no lighting.
- Virtually seamless transition from real wood blades to motor.


## Specs

Blade Sweep Opt (in.)	60
Blades	4
Blade Pitch (°)	16
Motor Size (MM)	125X30
Amps at High Speed	0.46
Watts (Hi Speed)	32.60
Energy Guide CFM	5532
Energy Guide CFM_Watts	170
High Speed (CFM)	5532
Low Speed (CFM)	2037
Carton Size (CU FT)	2.16

Bulb CCT 3000  
Bulb Wattage 17  
Light Kit Options Integrated Light Kit

## Dimensions

A:	16.62
A: (2° Downrod) -	16.62
B: (2° downrod)	15.69
C:	8.23
D:	5.51
E:	12.83
F: w/o Light Kit -	12.83
Downrod Length (in.)	6



## Downloads

### Ricasso - RIC60BNK

 [PDF Tear Sheet](#)

 [Energy Guide](#)

 [Energy Guide Image](#)