

FEISS

EST. 1955

F3170/6DWI: 6 - Light Chandelier



Dimensions:

Diameter: 37 1/8" **Overall Height:** 103 7/8"
Height: 37 1/8" **Wire:** 180" (color/Brown)
Weight: 22 lbs. **Chain:** 60"
Mounting Proc.: Center Lock-Up
Connection: Mounted To Box

Bulbs:

6 - Medium A19 60w Max. 120v - Not included

Features:

- Vintage lamp(s) recommended for aesthetics

Material List:

1 Body - Steel - Dark Weathered Iron

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3168-3-F3169-5-F3170-6)

Collection: Loras

UPC #: 014817570113

Finish: Dark Weathered Iron (DWI)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Clear Seeded	6				10	5 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/8			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3170/6DWI	1	014817570113	36	36.25	13	9.818	32.2	250	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

NJ Pallet		8		48	40	77	85.556	258.4		No
NV Pallet		8		48	40	77	85.556	258.4		No