

METROPOLITAN[®]

LIGHTING FIXTURE CO.

Item # N6772-293	UPC Code: 840254047662
Product Family Name: Coronade	Finish: Pandora Gold Leaf
Category: SEMI FLUSH	Category Type: Semi Flush
Certification 3057374	
Patents:	
Notes:	



Convertible to Semi Flush

Image File Name: **N6772-293.jpg**



MEASUREMENTS

Width: 16	Length: 18.0	Height: 7.75	Extension: Yes
Height Adjustable: Yes	Min Overall Height: 18.0	Max Overall Height: 54.0	Slope: Yes
Wire Length: 72"	Chain Length:	Safety Cable Included: No	Net Weight: 6.64
Canopy Width: 5.0	Canopy Height: 1.0	Canopy Length: 5.0	Center to Bottom:
Backplate Width:	Backplate Height:	Center to Top:	

LAMPING

No. of Bulbs: 4	Light Type: B10.5 CAND			
Max Bulb Wattage: 60	Socket: E12, CAND			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included:
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



SHIPPING

Carton Width: 18.5	Carton Height: 10.75	Carton Length: 18.5
Carton Weight: 9.42	Carton Cubic Feet: 2.129	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Damp Location



ETL Intertek

WARNING: Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.