



## Specification Sheet

# G40 Globe Incandescent Lamp

Order Number **03101**

### Specifications

Energy Used (Watts).....	40
Domestic Code.....	40G40
Volts.....	120
Brightness (Lumens) .....	431
Average Rated Hours .....	2500
Life (in years)* .....	2.3
Dimmable.....	Yes
Filament Type .....	CC6
Light Center Length (LCL) .....	3 7/8"
Estimated Yearly Energy Cost** .....	\$4.82
Country of Origin.....	China

### Physical Characteristics

Finish .....	Clear
Base.....	Medium
MOL.....	6 3/4"



\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
©“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

