

# CAT6 PATCH CABLE UNSHIELDED (BARE COPPER)




## DESCRIPTION

Category-6 Mold-Injection-Snagless Patch Cord, 24-AWG Stranded, PVC Jacket.

## FEATURES

- Bare Copper Stranded Conductors
- Unshielded RJ45 Modular Plugs
- 8P8C Gold Plated Pins 50U"
- 568B Wiring Color Code
- RoHS Compliant, UL



## SKU: 094-SERIES

### Conductor

Size	24AWG Stranded
Material	Bare Copper

### Jacket

Material	Flame Retardant PVC
Diameter	5.8±0.2mm

### Connectors

RJ45	8P/8C Gold Plated 50U"
------	------------------------

RoHS Compliant	Yes
Insulation Resistance	Min. 5000 MΩ Km
Conductor Resistance	Max. 9.38 Ω/100m

### Approvals

UL cUL Listed, ETL / 3P Certified ANSI/TIA-568-C.2 Category 6 standards.

Available in many colors.

**VERTICAL CABLE**

951.696.7772 California  
800.749.2447 Florida  
845.391.8318 New York



[www.verticalcable.com](http://www.verticalcable.com)

Rev. 04/2018  
Subject to change without notice.