



**Sunlite LED MR16 Mini Reflector  
2.2W (25WW Equivalent) Light Bulb  
(GU5.3) Base, White**

- These lamps can last up to 30,000 hours making them virtually maintenance free
- This 120 volts, 2.2 watt, MR16 mini reflector is extremely energy efficient and features a GU5.3 base
- Produces a spectacular white light at 220 lumens, using only 2.2 watts of energy
- Contains no mercury and doesn't release any hazardous gasses so there's no need to worry if a bulb breaks and no need for recycling as with CFLs
- Can fit right into your living room or into the most cutting edge, state of the art, lighting design project



**General Characteristics**

<b>Bulb</b>	MR16
<b>Lamp Type</b>	ECO
<b>Lamp Life Hours</b>	30000 Hours
<b>Bulb Finish</b>	Clear
<b>Base</b>	2-Pin (GU5.3)
<b>Lumens Per Watt (LPW)</b>	100.00
<b>Life (based on 3hr/day)</b>	27.4 Years
<b>Estimated Energy Cost</b>	\$0.26 per Year
<b>Ingress Protection</b>	IP20

**Electrical Characteristics**

<b>Watts</b>	2.2
<b>Volts</b>	120
<b>Equivalent Watts</b>	25
<b>Number of LEDs</b>	60
<b>Power Factor</b>	0.7

**Light Characteristics**

<b>Brightness</b>	220 Lumens
<b>Color Accuracy (CRI)</b>	75
<b>Light Appearance</b>	White
<b>Color Temperature</b>	6000K
<b>Beam Angle</b>	120°

**Product Dimensions**

<b>MOL (in)</b>	1.89
<b>Diameter (in)</b>	1.42
<b>Item Dimensions (in)</b>	(W) 2.55 (H) 2.46 (D) 2.55
<b>Package Dimensions (in)</b>	(W) 2.00 (H) 2.10 (D) 2.00

**Product Data**

<b>Item Number</b>	80097-SU
<b>Case Quantity</b>	12
<b>Barcode on SKU</b>	653703800974
<b>Barcode on Case</b>	10653703800971
<b>Brand</b>	SUNLITE
<b>Description</b>	MR16/60LED/2.2W/GU5.3/W/120V