



# LED A-Lamps

**OMNI-DIRECTIONAL • ALL-PURPOSE • 3-WAY**

TCP's LED A-lamps provide the lighting you need at a cost you will love. Advanced factory techniques and rigorous testing ensure each lamp is perfect from day one. Install a LED A-lamp wherever you would a traditional lamp and see the improvement.



## LIMITLESS OPTIONS FOR THE FOLLOWING APPLICATIONS

- General lighting
- Floor lamps
- Ceiling fixtures
- Table lamps
- Sconces

### FEATURES

Up to 85% less energy than halogen alternatives

Long life

Very low heat generation

Excellent color consistency and CRI

UL approved for damp location

Durable plastic housing

ANSI construction compliant

### BENEFITS

Instant energy savings

Minimizes replacement and maintenance costs

Perfect for sensitive display lighting such as art galleries

Enhances colors of focal point while maintaining uniformity throughout lighting installation from lamp to lamp

Can be used outdoors when protected from elements—withstands humidity indoors/outdoors

Lower the risk of injury and breakage

Fits all A-lamp installations

Dims to ≤ 10% of full light level when applicable

## SPECIFICATIONS


Input Line Voltage ..... 120 VAC  
 Input Line Frequency ..... 50/60HZ  
 Lamp Life (Rated) ..... 10,000, 15,000, 20,000 or 25,000 hour options  
 Minimum Starting Temp ..... -30°C  
 Maximum Operating Temp ..... 40°C  
 CRI ..... 80

Suitable for use in totally enclosed fixtures.  
 (Vapor tight or jelly jar applications may reduce life)

\*Based on 12 hours use per day

Do not use more than 2 bulbs in an enclosed fixture.

If fixture is manufactured for incandescent bulbs, use no higher than the LED equivalent wattage, as shown on this spec sheet.



**1 YEAR WARRANTY\***  
10,000 HOUR LAMPS

**3 YEAR WARRANTY\***  
15,000 HOUR LAMPS

**5 YEAR WARRANTY\***  
25,000 HOUR LAMPS

we know light.™





# LED A-Lamps

OMNI-DIRECTIONAL • ALL-PURPOSE • 3-WAY

ITEM #	DESCRIPTION	ENERGY STAR	VOLTAGE	WATTS	INCANDESENT WATTS	LPW	LUMENS	COLOR	HOURS	CRI	MOL (inches)	DIA (inches)	WARRANTY BASE	WARRANTY YEARS	CASE QUANTITY
<b>LED 40W Equivalent Options</b>															
<b>6W A19 A-Lamp • Non-Dimmable • 15,000 Hour</b>															
L6A19N1527K	LED 6W A19 ND 2700K	★	120	6	40	80.0	480	2700K	15,000	80	4.0	2.2	E26	3	12
L6A19N1530K	LED 6W A19 ND 3000K	★	120	6	40	80.0	480	3000K	15,000	80	4.0	2.2	E26	3	12
L6A19N1541K	LED 6W A19 ND 4100K	★	120	6	40	80.0	480	4100K	15,000	80	4.0	2.2	E26	3	12
L6A19N1550K	LED 6W A19 ND 5000K	★	120	6	40	80.0	480	5000K	15,000	80	4.0	2.2	E26	3	12
<b>6W A19 A-Lamp • Dimmable • 25,000 Hour</b>															
L6A19D2524K	LED 5.5W A19 DIM 2400K		120	6	40	62.5	375	2400K	25,000	80	4.0	2.2	E26	5	12
L6A19D2527K	LED 5.5W A19 DIM 2700K	★	120	6	40	80.0	480	2700K	25,000	80	4.0	2.2	E26	5	12
L6A19D2530K	LED 5.5W A19 DIM 3000K	★	120	6	40	80.0	480	3000K	25,000	80	4.0	2.2	E26	5	12
L6A19D2541K	LED 5.5W A19 DIM 4100K	★	120	6	40	83.3	500	4100K	25,000	80	4.0	2.2	E26	5	12
L6A19D2550K	LED 5.5W A19 DIM 5000K	★	120	6	40	87.5	525	5000K	25,000	80	4.0	2.2	E26	5	12
<b>LED 60W Equivalent Options</b>															
<b>9.5W A19 A-Lamp • Non-Dimmable • 10,000 Hour</b>															
L9A19N1027K4	LED 9.5W A19 ND 2700K 4 PACK		120	9.5	60	84.2	800	2700K	10,000	80	4.3	2.4	E26	1	12
L9A19N1030K4	LED 9.5W A19 ND 3000K 4 PACK		120	9.5	60	84.2	800	3000K	10,000	80	4.3	2.4	E26	1	12
L9A19N1041K4	LED 9.5W A19 ND 4100K 4 PACK		120	9.5	60	84.2	800	4100K	10,000	80	4.3	2.4	E26	1	12
<b>9W A19 A-Lamp • Non-Dimmable • 15,000 Hour</b>															
L60A19N1527K	LED 9W A19 ND 2700K	★	120	9	60	88.9	800	2700K	15,000	80	4.3	2.4	E26	3	12
L60A19N1530K	LED 9W A19 ND 3000K	★	120	9	60	88.9	800	3000K	15,000	80	4.3	2.4	E26	3	12
L60A19N1541K	LED 9W A19 ND 4100K	★	120	9	60	94.4	850	4100K	15,000	80	4.3	2.4	E26	3	12
L60A19N1550K	LED 9W A19 ND 5000K	★	120	9	60	94.4	850	5000K	15,000	80	4.3	2.4	E26	3	12
<b>9W A19 A-Lamp • Dimmable • 15,000 Hour</b>															
L9A19D1527K	LED 9W A19 DIM 2700K	★	120	9	60	88.9	800	2700K	15,000	80	4.3	2.4	E26	3	12
L9A19D1527K24	LED 9W A19 DIM 2700K 24 PACK	★	120	9	60	88.9	800	2700K	15,000	80	4.3	2.4	E26	3	-
L9A19D1530K	LED 9W A19 DIM 3000K	★	120	9	60	88.9	800	3000K	15,000	80	4.3	2.4	E26	3	12
L9A19D1541K	LED 9W A19 DIM 4100K	★	120	9	60	91.7	825	4100K	15,000	80	4.3	2.4	E26	3	12
L9A19D1550K	LED 9W A19 DIM 5000K	★	120	9	60	91.7	825	5000K	15,000	80	4.3	2.4	E26	3	12
<b>9W A19 A-Lamp • Dimmable • 25,000 Hour</b>															
L9A19D2524K	LED 9W A19 DIM 2400K		120	9	60	77.7	700	2400K	25,000	80	4.3	2.4	E26	5	12
L9A19D2527K	LED 9W A19 DIM 2700K	★	120	9	60	88.9	800	2700K	25,000	80	4.3	2.4	E26	5	12
L9A19D2530K	LED 9W A19 DIM 3000K	★	120	9	60	88.9	800	3000K	25,000	80	4.3	2.4	E26	5	12
L9A19D2541K	LED 9W A19 DIM 4100K	★	120	9	60	91.7	825	4100K	25,000	80	4.3	2.4	E26	5	12
L9A19D2550K	LED 9W A19 DIM 5000K	★	120	9	60	91.7	825	5000K	25,000	80	4.3	2.4	E26	5	12
<b>9W A19 A-Lamp • Allusion Dimmable • 25,000 Hour</b>															
LED9A19DA	LED 9W A19 2000K - 2700K ALLUSION		120	9	60	72.2	650	2000K-2700K	25,000	80	4.6	2.4	E26	5	12
<b>9.5W A19 Omni-Directional A-Lamp GU24 • Dimmable • 25,000 Hour</b>															
LED10A19GUDOD27K	LED 9.5W A19 DIM OMNI 27K GU24	★	120	9.5	60	84.2	800	2700K	25,000	80	4.4	2.4	E26	5	12
LED10A19GUDOD30K	LED 9.5W A19 DIM OMNI 30K GU24	★	120	9.5	60	84.2	800	3000K	25,000	80	4.4	2.4	E26	5	12
LED10A19GUDOD41K	LED 9.5W A19 DIM OMNI 41K GU24	★	120	9.5	60	84.2	800	4100K	25,000	80	4.4	2.4	E26	5	12

continued next page



# LED A-Lamps

OMNI-DIRECTIONAL • ALL-PURPOSE • 3-WAY

ITEM #	DESCRIPTION	ENERGY STAR	VOLTAGE	INCANDESCENT		LPW	LUMENS	CCT	HOURS	CRI	MOL (inches)	DIA (inches)	BASE	WARRANTY YEARS	CASE QUANTITY
				WATTS	WATTS										

## LED 75W Equivalent Options

### 13.5W A19 A-Lamp • Non-Dimmable • 15,000 Hour

L11A19N1527K	LED 13.5W A19 ND 2700K	★	120	13.5	75	81.5	1100	2700K	15,000	80	4.4	2.4	E26	3	12
L11A19N1530K	LED 13.5W A19 ND 3000K	★	120	13.5	75	81.5	1100	3000K	15,000	80	4.4	2.4	E26	3	12
L11A19N1541K	LED 13.5W A19 ND 4100K	★	120	13.5	75	81.5	1100	4100K	15,000	80	4.4	2.4	E26	3	12
L11A19N1550K	LED 13.5W A19 ND 5000K	★	120	13.5	75	81.5	1100	5000K	15,000	80	4.4	2.4	E26	3	12

### 13.5W A19 A-Lamp • Dimmable • 25,000 Hour

L11A19D2527K	LED 13.5W A19 DIM 2700K	★	120	13.5	75	81.5	1100	2700K	25,000	80	4.4	2.4	E26	5	12
L11A19D2530K	LED 13.5W A19 DIM 3000K	★	120	13.5	75	81.5	1100	3000K	25,000	80	4.4	2.4	E26	5	12
L11A19D2541K	LED 13.5W A19 DIM 4100K	★	120	13.5	75	81.5	1100	4100K	25,000	80	4.4	2.4	E26	5	12
L11A19D2550K	LED 13.5W A19 DIM 5000K	★	120	13.5	75	81.5	1100	5000K	25,000	80	4.4	2.4	E26	5	12

## LED 100W Equivalent Options

### 14W A19 A-Lamp • Non-Dimmable • 10,000 Hour

L16A19N1027K4	LED 14W A19 ND 2700K 4PK		120	14	100	107.1	1500	2700K	10,000	80	4.7	2.6	E26	1	12
L16A19N1041K4	LED 14W A19 ND 4100K 4PK		120	14	100	107.1	1500	4100K	10,000	80	4.7	2.6	E26	1	12

### 15.5W A19 A-Lamp • Non-Dimmable • 15,000 Hour

L16A19N1527K	LED 15.5W A19 ND 2700K	★	120	15.5	100	103.2	1600	2700K	15,000	80	4.7	2.6	E26	3	12
L16A19N1530K	LED 15.5W A19 ND 3000K	★	120	15.5	100	103.2	1600	3000K	15,000	80	4.7	2.6	E26	3	12
L16A19N1541K	LED 15.5W A19 ND 4100K	★	120	15.5	100	103.2	1600	4100K	15,000	80	4.7	2.6	E26	3	12
L16A19N1550K	LED 15.5W A19 ND 5000K	★	120	15.5	100	103.2	1600	5000K	15,000	80	4.7	2.6	E26	3	12

### 15W A19 A-Lamp • Dimmable • 15,000 Hour

L15A21D1527K	LED 15W A19 DIM 2700K	★	120	15	100	106.7	1600	2700K	15,000	80	4.7	2.6	E26	3	12
L15A21D1530K	LED 15W A19 DIM 3000K	★	120	15	100	106.7	1600	3000K	15,000	80	4.7	2.6	E26	3	12
L15A21D1541K	LED 15W A19 DIM 4100K	★	120	15	100	106.7	1600	4100K	15,000	80	4.7	2.6	E26	3	12
L15A21D1550K	LED 15W A19 DIM 5000K	★	120	15	100	106.7	1600	5000K	15,000	80	4.7	2.6	E26	3	12

### 15W A19 A-Lamp • Dimmable • 25,000 Hour

L15A19D2527K	LED 15W A19 DIM 2700K	★	120	15	100	106.7	1600	2700K	25,000	80	4.7	2.6	E26	5	12
L15A19D2530K	LED 15W A19 DIM 3000K	★	120	15	100	106.7	1600	3000K	25,000	80	4.7	2.6	E26	5	12
L15A19D2541K	LED 15W A19 DIM 4100K	★	120	15	100	106.7	1600	4100K	25,000	80	4.7	2.6	E26	5	12
L15A19D2550K	LED 15W A19 DIM 5000K	★	120	15	100	106.7	1600	5000K	25,000	80	4.7	2.6	E26	5	12

## LED 40/60/100 3-Way Equivalent Options

### 4/8/16W A21 3-Way A-Lamp • Dimmable • 25,000 Hour

LED16A21D3WAY27K	LED 16W A21 DIM 2700K 3WAY	★	120	4/8/16	40/60/100	120/100/100	480/800/1600	2700K	25,000	80	4.9	2.6	E26	5	12
LED16A21D3WAY30K	LED 16W A21 DIM 3000K 3WAY	★	120	4/8/16	40/60/100	120/100/100	480/800/1600	3000K	25,000	80	4.9	2.6	E26	5	12
LED16A21D3WAY41K	LED 16W A21 DIM 4100K 3WAY	★	120	4/8/16	40/60/100	120/100/100	480/800/1600	4100K	25,000	80	4.9	2.6	E26	5	12
LED16A21D3WAY50K	LED 16W A21 DIM 5000K 3WAY	★	120	4/8/16	40/60/100	120/100/100	480/800/1600	5000K	25,000	80	4.9	2.6	E26	5	12

## LED 60W Wet Location Equivalent Options

### 9.5W A19 Omni-Directional Wet Location A-Lamp • Dimmable • 25,000 Hour

LED10A19D0D27KW	LED 9.5W A19 DIM OMNI 27K WET	★	120	9.5	60	84.2	800	2700K	25,000	80	4.6	2.5	E26	5	12
LED10A19D0D30KW	LED 9.5W A19 DIM OMNI 30K WET	★	120	9.5	60	86.8	825	3000K	25,000	80	4.6	2.5	E26	5	12
LED10A19D0D41KW	LED 9.5W A19 DIM OMNI 41K WET	★	120	9.5	60	89.5	850	4100K	25,000	80	4.6	2.5	E26	5	12
LED10A19D0D50KW	LED 9.5W A19 DIM OMNI 50K WET	★	120	9.5	60	89.5	850	5000K	25,000	80	4.6	2.5	E26	5	12

# TECHNOLOGY CAST IN A BEAUTIFUL LIGHT

For over 20 years, TCP has been designing, developing and delivering energy-efficient lighting into the market. Thanks to our cutting-edge technology and manufacturing expertise, we have shipped billions of high quality lighting products. With TCP, you can count on a lighting product that is designed to meet the needs of the market — that transforms your surroundings and envelopes you in warmth — lighting that generates beauty with every flip of the switch.

# LED