

# Specification Sheet

## R14 Reflector Incandescent Lamp

Item Number **03626**

### Specifications

Energy Used (Watts).....	40
Domestic Code.....	40R14/IN/FL
Volts.....	120
Beam Type.....	Flood
Filament Type .....	CC2V
Light Center Length (LCL) .....	1 7/8"
Brightness (Lumens) .....	185
Average Rated Hours .....	1500
Life (in years)*.....	1.4
Estimated Yearly Energy Cost**.....	\$4.82
Country of Origin.....	China



### Physical Characteristics

Finish .....	Frost
Base .....	E17 (Intermediate)
MOL.....	2 5/8"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
 © "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation

