



## Specification Sheet

# G16 1/2 Globe Incandescent Lamp

Order Number **03840**

### Specifications

Energy Used (Watts).....	60
Domestic Code.....	60G161/2/W/CB
Volts.....	120
Brightness (Lumens) .....	580
Average Rated Hours .....	1500
Life (in years)* .....	1.4
Dimmable.....	Yes
Filament Type .....	CC2V
Light Center Length (LCL) .....	1 3/4"
Estimated Yearly Energy Cost** .....	\$7.23
Country of Origin.....	China



### Physical Characteristics

Finish .....	White
Base .....	Candelabra
MOL.....	2 3/4"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
©“Westinghouse” and “You can be sure...if it's Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

