



# S8643

8MR16/LED/40'/40K/90CRI/12V  
 8 watt; LED MR16; 4000K; 40' beam spread; GU5.3 base; 12 volts

### Features

- Silver back MR16 reflector
- Direct replacements for 75 watt Halogen lamps - uses only 8 watts
- Dimmable
- No UV or IR radiation
- Approved for enclosed fixtures\*



S8643

/>  
 \*reference warranty for hours per day of operation

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S8643	045923086434	12	8	75	0.93	MR16	GU5.3

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
8MR16/LED/40'/40K/90CRI/12V	Dimmable	<a href="#">Compatible dimmers for S8643</a>	Silver Back	1-7/8"	2"	490	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	ENERGY STAR	CEC Status	RoHS Compliant
4000	Cool White	90+	40	-25C (-13F) to a maximum of +45C (+113F)	ENERGY STAR	Lawful for sale in California	Yes

UL Classification	Warranty
cULus - Damp Location Rated	<a href="#">5 Year Limited - 10 hour use per day</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

