

Search Parameters:
[e-Catalog](#) > [Starters](#) > IEC
Starters, IEC

Product #: GPS1BHAG

Short Description: GPS1BHAG

SPECIFICATIONS

Category	Manual Motor Starter - SURION
Rated Current	2 A
Capacity	GPS1BH - High breaking capacity
Instantaneous short-circuit release (A)	32
Rated power 3 phase motors at 220/230Vac Pn (hp)	1/2
Rated power 3 phase motors at 400Vac Pn (hp)	1/2
Rated power 3 phase motors at 440Vac Pn (hp)	1
Rated power 3 phase motors at 500/525Vac Pn (hp)	1 1/2
Rated power 3 phase motors at 660/690Vac Pn (hp)	1 hp
Rated service short-circuit breaking cap 220/230V Ics kA	100
Rated service short-circuit breaking cap 400V Ics kA	50
Rated service short-circuit breaking cap 440V Ics kA	10
Rated service short-circuit breaking cap 500/525V Ics kA	100
Rated service short-circuit breaking cap 600V Ics kA	6
Rated service short-circuit breaking cap 690V Ics kA	6
Rated ultimate short-circuit breaking cap 220/230V Icu kA	100
Rated ultimate short-circuit breaking cap 400V Icu kA	25
Rated ultimate short-circuit breaking cap 440V Icu kA	25
Rated ultimate short-circuit breaking cap 500/525V Icu kA	100
Rated ultimate short-circuit breaking cap 600V Icu kA	8
Rated ultimate short-circuit breaking cap 690V Icu kA	8
Series	Surion - GPS1B - Thermal and magnetic protection (Ie max 32A)
Thermal current setting range (A)	1 - 2.5 A
Trip class IEC 60947-4-1	Class 10
Weight	0.792 lb
Single Phase Horsepower @ 230V	1/6
FLA Adjustment Range	1 - 2.5 A
Max. Fuse Size (A)	10
Max Circuit Breaker Size (A)	15
Max. Fuse or Circuit Breaker Size - Group Installation (A)	500
Rated Breaking Capacity @ 277Y/480V - Combination Starter (kA)	50
Minimum Contactor Size	CL00 or MC0
Width	45.0 mm
GSA Compliance	No
GO Schedule	CC
UPC	453891501240
List Price	\$125



[View Larger](#)

Publications/Resources

[GPS1BHAG](#)

Additional Resources for Manual Motor Starter - SURION

[Control Log : 6-6](#)

- MANUAL MOTOR STARTER T+M PROT. GPS1 1.6-2.5A HIGH BREAKING
 - Pack-5

Products

[Critical Power](#)
[Drives and Controls](#)
[Electrical Distribution](#)
[New Products](#)

Services

[Aftermarket Solutions](#)
[Arc Flash Services](#)
[Critical Power Services](#)
[Drives Services](#)
[Emergency Services](#)
[Engineering Services](#)
[Hydro Services](#)
[Industrial Service Centers](#)
[Inspection Services](#)

Markets

[Commercial](#)
[Data Center](#)
[Health Care](#)
[Industrial](#)
[Mining](#)
[Oil & Gas](#)
[Telecom](#)

Resources

[Publication Library](#)
[Project Assistant 2.0](#)
[Videos](#)
[Social Media & Apps](#)
[Data Visualization](#)
[Counterfeit Beat](#)
[Newsletter Subscriptions](#)
[e-Catalog](#)
[GE Smart Catalog](#)

Your Business

[Contractor](#)
[Distributor](#)
[Electrical Maintenance Org.](#)
[Facilities Operations](#)
[Original Equipment Mfr.](#)
[Consulting / Design Engineer](#)

News & Events

Where To Buy