

Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs - Type BQ, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. 2-Pole Common-Trip circuit breaker type BQ. Rated 120/240V (070A) (AIR 10 kA). Special features: Load side lugs are included.



Number of poles	2
Suitability for operation	Electrical Distribution
<b>Electricity</b>	
Continuous current rated value	70 A
<b>Model</b>	
product brandname	SIEMENS
Special product feature	Auxiliary Switch 24V
Type of electrical connection	BOLT-ON
<b>Mechanical Design</b>	
Depth [in]	4 in
Design of the product	BQ
Height [in]	2 in
Width [in]	3 in
<b>General product approval</b>	
Standard	UL 489
<b>last modified:</b>	11/09/2017