



Superstrut[®]

Metal Channels

T&B Catalog Number:

A1200HS 10HDG

UPC Number:

61601310109

Status:


Active

Description:

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 10 Feet, Half Slotted Hot-Dip Galvanized Steel with 9/16 Inch x 1-1/8 Inch Slots on 2 Inch Centers

Application

Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire



General

Material	Steel
Finish	Hot-Dip Galvanized

Dimension Information

Length (feet)	10
Dimensions (inches)	1-5/8 x 1-5/8
Slot Size (inches)	9/16 x 1-1/8
Slot Spacing On Centers (inches)	2
Material Thickness (ga.)	12

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	500
T&B Sold in UOM	Feet
T&B Weight Per UOM	185 lbs. per 100

Application Support

MSDS Number	sds-00046-tb2
Metal Framing Channels-Series 1000	Available on Website
Finishes	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com