



## Pool & Spa: Mechanical Controls

### T104R201 | 24-Hour Mechanical Time Switch in Enclosure with Pool Heater Protection



## T104R201

### 24-HOUR MECHANICAL TIME SWITCH IN ENCLOSURE WITH POOL HEATER PROTECTION

Heavy-duty mechanical time switches control a single load



#### Features & Applications

#### Features

- Highest motor load ratings in the industry
- 12 ON/OFF operations per day

#### Applications

- Pumps
- Lighting

- ON/OFF trippers included
- Available with pool heater protection
- Teeter-type terminals for multiple load connections
- Heaters

## Specifications

### Maximum ON/OFF Operations

12

### Operation Mode

24-hour

### Has Override Switch

No

### Input Voltages Display

208-277 VAC, 60 Hz

### Electronic Ballast

16 A, 277 VAC, 60 Hz

### Motor

2 HP, 24 FLA, 120 VAC, 60 Hz

5 HP, 28 FLA, 240 VAC, 60 Hz

### Enclosure Type

Outdoor Type 3R Metal

### Number of Trippers Included

0

### Number of Circuits

1

### Maximum Power Consumption (W)

3 W

### Switch Type

DPST

### Operating Temperature Max (°C)

54

### Operating Temperature Max (F)

130

### Operating Temperature Min (°C)

-40

### Operating Temperature Min (F)

-40

### Warranty

1-year

## Related Accessories and Parts (2)



156T1978A

**1 SET OF ON/OFF TRIPPERS FOR T100,  
T7000, AND WH40**

124--00066

**INSULATOR FOR 3-CIRCUIT TIMERS**

---

Copyright © 2017 Intermatic Incorporated. All rights reserved.