

## OL5420BK: 1 - Light Wall Lantern



### Dimensions:

**Width:** 6 1/2"      **Extends:** 7 3/4"  
**Height:** 11 1/2"      **Wire:** 8"  
**Weight:** 3.19 lbs.      **Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box

### Bulbs:

1 - Medium A19 100w Max. 120v - Not included

### Features:

•

### Material List:

1 Body - Aluminum - Black

### Safety Listing:

Safety Listed for Wet Locations  
 Safety Listed for Wet Locations

### Instruction Sheets:

English (2019)  
 Trilingual (English, Spanish, and French) (2019)

**Collection:** Cotswold Lane

The classic styling of the Cotswold Lane lighting collection by Feiss features the look of dentil molding at the top of each pane of beveled glass which adds to the more formal, traditional aesthetic of this antique gas lantern-inspired collection. The LED option features advanced, warm-on-dim LED technology that warms in color when dimmed, going from 2700K to 2200K and is California Title 24 compliant. Cotswold Lane is available in three finish options: Black with Clear Beveled glass, Grecian Bronze with Clear Beveled glass and Black with Clear Seeded glass.

**UPC #:** 014817573992

**Finish:** Black (BK)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Seeded	4			1	5 3/4					

Panel	Glass	Clear Seeded	4			3 1/2	5 3/4				
-------	-------	--------------	---	--	--	-------	-------	--	--	--	--

**Backplate / Canopy Details:**

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	8 1/8	5 1/8			3 1/2	

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	OL5420BK	1	014817573992	14.25	10.75	9.25	0.82	4.3	175	Yes
Master Pack	OL5420BK	2	10014817573999	19	15.25	11	1.844	9.7	175	Yes
NJ Pallet		80		48	40	77	85.556	388		No
NV Pallet		80		48	40	77	85.556	388		No