

## SPECIFICATION & FEATURES

### DESCRIPTION:

Orbit Industries' 2-3/4" Gangable Switch Boxes are used in the installation of switches. Models include a pre-assembled 10-32 grounds screw and a solid #12AWG 7" Pigtail for ground applications. The 2-Gang gangable switch boxes can be expanded to multigangs by adding one or more GMB-1-NE units to the non-bracketed side. Orbit Industries' selection includes a variety of gangable switch boxes with non-metallic cable clamps, metal clad cable clamps, and old work tigergrrips. The wide tigergrip design is a non-gangable wide old-work switch box for easy installation of GFCI or other large devices. Use with a Midi or Oversized switch plate.

### CERTIFICATION:

UL file E227970, conforms to UL514A.

### FEATURES

#### Pigtail Features:

**PT:** 7" Solid Cu. #12AWG Pigtail Pre-assembled with Ground Emboss and 10-32 Ground Screw

#### Knockout:

**50:** 1/2" K.O.; **Loom:** Loom Pryouts; **MKO:** Moon K.O. (1/2" and 3/4" K.O.)

#### Bracket:

**FB:** (L: 7-1/4", W: 3/4") Offset (9/16") Mounts on flat side of stud or joist

**B:** (L: 3", W: 2") Offset (9/16") Face mounts on front edge of wood stud

#### Clamp:


**BX/MC:** Accommodates Metal Clad Cables from size #14-2 to #10-4. All MC series boxes are suitable for use with MCAP™-Aluminum (MCAP is a trademark of Southwire Company)

**NM:** Accommodates #14-2 to #10-3 Non-Metallic Cables with ground

#### TGMW Features:

Non-gangable wide old-work switch box for easy installation of GFCI or other large devices  
Use with Mid-Size or Jumbo Wallplates

## GANGABLE SWITCH BOXES 2-3/4" DEEP



### DIMENSIONS

**Width:** 2" OR 4"

**Height:** 3"

**Depth:** 2-3/4"

**Cu.In.:** 14.0 OR 28.0

(For TGMW 2-1/4" W x 3" H, 18.5 Cu.In.)

### CONFIGURATION DATA

Catalog No.	Description	Knockouts			Std. Pkg.
		Sides	Ends	Bottom	
GMB-1-NE	No Ears, With Leveling Bumps	(2)-1/2"	(2)-MKO	(2)-1/2"	50
GMB-1	Ears Only	(4)-1/2"	(2)-MKO	(2)-1/2"	50
WMB-PT	Wide Old Work (Non-Gangable) Must be used with Mid-Size or Jumbo Wall Plate	(4)-1/2"	(2)-MKO	(2)-1/2"	50
GMB-2-B	With B Bracket	(2)-1/2"	(4)-MKO	(4)-1/2"	25
GMB-1-FB	With FB Bracket(9/16" Setback)	(2)-1/2"	(2)-MKO	(2)-1/2"	50
GMB-2-FB	With FB Bracket(9/16" Setback)	(2)-1/2"	(4)-MKO	(4)-1/2"	25
GMB-1-NM	With NM Cable Clamps	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-1-NM-B	NM Cable Clamps & B Bracket (9/16" Setback)	(2)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-1-NM-FB	NM Cable Clamps & FB Bracket (9/16" Setback)	(2)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-2-NM-FB	NM Cable Clamps & FB Bracket (9/16" Setback)	(2)-1/2"	(4)-1/2", (8)-Loom	(2)-1/2"	25
GMB-1-NM-OW	With NM Cable Clamps, Old Work Grips	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-1-MC	With BX/MC Cable Clamps	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-1-MC-B	BX/MC Clamps & B Bracket (9/16" Setback)	(2)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-1-MC-FB	BX/MC Clamps & F B Bracket (9/16" Setback)	(2)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
GMB-2-MC-FB	BX/MC Clamps & F B Bracket (9/16" Setback)	(2)-1/2"	(4)-1/2", (8)-Loom	(2)-1/2"	25
GMB-1-MC-OW	With MC Cable Clamps, Old Work Grips	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
SGM-1	Gangable Old Work switch box	(4)-1/2"	(2)-MKO	(2)-1/2"	50
SGM-1-NM	Gangable Old Work NM switch box	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
SGM-1-MC	Gangable Old Work BX/MC Switch Box	(4)-1/2"	(2)-1/2", (4)-Loom	(1)-1/2"	50
TGMW	Wide Old Work Tigergrip (Non-Gangable) Must be used with Mid-Size or Jumbo Wall Plate	(4)-1/2"	(2)-1/2"	(2)-1/2"	50

