



U5210-XL-75



Unmetered Small Closing Plate TT30 1450 520GR Single Pedestal Pad Mount

SPECIFICATIONS

Brand Name	Milbank
Type	Unmetered Power Supply
Special Features	Single Pole 20 Ampere Breaker and Single Pole 30 Ampere Breaker and Double Pole 50 Ampere Breaker
Application	RV Power
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	5.188L x 8.656W x40.5H
Number of	3

Main Breakers	
Main Breaker Size	One Single Pole 20 Ampere Breaker and One Single Pole 30 Ampere Breaker and One Double Pole 50 Ampere Breaker
Cable Entry	Underground
Terminal	Double Mechanical
Insulation	Glass Polyester
Mounting	Pedestal
Material	G90 Galvanized Steel with Powder Coat Finish
Number of Jaws	4 Terminal
Bypass Provision	No Bypass
Number of Meter Positions	Single Power Head
Equipment Ground	2 Barrel Ground Lug and Ground Bar
Hub/Closing Plate	Small Closing Plate
Line Side Wire Range	6 AWG - 350 kcmil
Number Branch Circuits	2

CIRCUITS

Number of Receptacles	3
-----------------------	---

Receptacle Configuration	One NEMA 14-50 and One NEMA TT30 and One NEMA 5-20 Ground Fault
--------------------------	---

Height	40.5 IN
--------	---------

Length	5.188 IN
--------	----------

Width	8.656 IN
-------	----------

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.