

# Omnidirectional A19 2700K, 800lm LED Lamp

- Omnidirectional bulb - shadow-free, even light distribution
- LED replacement for 60W incandescent bulbs
- 2700K - soft white
- Compatible with most commercial dimmers\*
- Energy efficient, long-lasting LED - over 85% reduction in energy costs compared to incandescent bulbs
- 15,000 hour design lifetime
- 3-year limited warranty

\* Dimming range may vary based on dimmer used.



Specifications	
Lamp Type	A19 2700K, 800lm
Model	A19-L800-C27-OD-D-E
Part Number	99873
Color Temperature	2700K
Lumen Output	800lm
Wattage	9W
Replacement Equivalent	60W Incandescent equivalent
CRI	80
Efficacy	76lm/W
Beam Angle	220°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to +40°C
Base	E26
Weight	2.24 oz.
Dimensions	2.38 x 4.43 x 2.38 in
Design life	15,000 Hours
Warranty	3-Year Limited Warranty

## Certifications:





# Omnidirectional A19 2700K, 800lm LED Lamp

## Additional Images:



## Diagrams:



## Lighting Facts:

Lighting Facts <small>Per Bulb</small>	
Information concernant l'éclairage <small>Pour une ampoule</small>	
Brightness/Luminosité	800 lumens
Estimated Yearly Energy Cost	\$1.08
Estimation Des Coûts Énergétiques Annuels	
<small>Based on 3 hrs/day, 11¢/kWh Sur la base de 3 heures / jour, 11 ¢ / kWh Cost depends on rates and use Le coût dépend du tarif et de l'utilisation</small>	
Life/Durée de vie	13.6 years/années
<small>Based on 3 hrs/day Sur la base de 3 heures/jour</small>	
Light Appearance/Degré de luminosité	
Warm/Chaude	Cool/Froide
2700 K	
Energy Used/Energie utilisée	9 watts