

Accent 1-Lt 120V

15231AZT (Textured Architectural Bronze)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Dimensions

| | |
|--------|-------|
| Height | 6.25" |
| Length | 7.25" |
| Width | 4.00" |

Alternate Lamps

| Lamp Included | Bulb Listing | Light Source | Max Wattage/Range | Bulb Product ID | Dimming |
|---------------|--------------|--------------|-------------------|-----------------|---------|
| No | Alternate | HIDV | 50W | | |

Ordering Information

| | |
|--------------------|-------------------------------|
| Product ID | 15231AZT |
| Finish | Textured Architectural Bronze |
| Available Finishes | AZT, BKT |

Specifications

| | |
|----------------------|-----------------------------|
| Material | Aluminum |
| Diffuser Description | Tempered Convex Clear Glass |

Electrical

| | |
|------------------|-------|
| Voltage | 120V |
| Lead Wire Length | 8.00" |

Qualifications

| | |
|--------------|--|
| Safety Rated | Wet |
| Warranty | www.kichler.com/warranty |

Primary Lamping

| | |
|------------------------|--------------|
| Light Source | Incandescent |
| Lamp Included | Not Included |
| # of Bulbs/LED Modules | 1 |
| Max or Nominal Watt | 50W |
| Socket Wire | 105 |
| Socket Type | Medium |
| Lamp Type | R20 |

Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.