



S9995

11.5T8U6/LED/22.5-835/DR
11.5 watt T8 U-Bend LED; 50000 average rated hours; Medium bi-pin base; 1700 lumens; 3500K



Features

- Direct Replacement - for use on Instant Start and Rapid Start ballasts with no rewiring required*
- Solid State LED lighting
- High efficacy
- Long life

*May not be compatible with all electronic ballasts.
Ballast required

S9995

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable
S9995	045923099953	11.5	T8	Medium Bi-Pin	G13	11.5T8U6/LED/22.5-835/DR	Non-Dimmable

Finish	MOL In Inches	MOD In Inches	Leg Spacing	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
White	22.5"	7.00"	6"	1700	50000	3500	Neutral White

CRI	Beam Spread Deg	Pack	Package Type	DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification
82	230	12	Box	P7FFNP8G DLC Search	Yes	Yes	cULus - Damp Location Rated



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

