

Project	
Schedule	Date
Notes	
Catalog Number	

Downlight CRI90

**Product Description**

naturalLED<sup>®</sup> retrofit Downlights are a simple LED lighting solution to replace 50W to 90W incandescent lamps. Designed as an energy efficient lighting solution for the industry's most popular 4" to 6" recessed downlight fixtures.

Easy installation and certified Air-Tight, our retrofit recessed Downlights are dimmable, CRI 90 rated, come with an E26 adapter, or may be hard wired. The 5/6" Model had torsion clips that are adjustable and will easily fit in a 5" or 6" recessed can.



**Features & Benefits**

- ▶ Energy Star Certified
- ▶ UL Wet
- ▶ Certified Air-Tight per ASTM E283-04
- ▶ Meets CEC Standards
- ▶ Excellent thermal design
- ▶ Built-in power connector with adjustable torsion clips

**Specifications**

- ▶ Input line voltage: 120
- ▶ CRI: 90
- ▶ Dimmable 5%-100%
- ▶ Beam Angle: Flood
- ▶ Operating temperature: -4°F ~ 104°F
- ▶ Available in 4" and 5/6" standard recess can

**Applications**

- ▶ Residential
- ▶ Retail Stores
- ▶ Schools & Universities
- ▶ Restaurants
- ▶ Hospitality

**Optional Accessories**

- ▶ GU24 Base



- ▶ Trim Options



**Included with downlight**

- ▶ E26 Base



Ordering Information

Code	Description	CCT	Watt	Lumen	Equiv Wattage	Size	CRI	Dim	Rated Hrs	WET RATED LOCATION	ENERGY STAR
7688	LED4RL9-54L930	3000K	9	540	60	4-inch	90	Yes	50,000	•	•
7689	LED4RL9-54L940	4000K	9	540	60	4-inch	90	Yes	50,000	•	•
7690	LED4RL9-54L950	5000K	9	540	60	4-inch	90	Yes	50,000	•	•
7691	LED6RL15-110L930	3000K	15	1,100	120	5/6-inch	90	Yes	50,000	•	•
7692	LED6RL15-110L940	4000K	15	1,100	120	5/6-inch	90	Yes	50,000	•	•
7693	LED6RL15-110L950	5000K	15	1,100	120	5/6-inch	90	Yes	50,000	•	•

Accessories (available for purchase)

Base

**P10029 ADP-RLGU24-N**  
(GU24 Socket Adaptor for LED Recessed Retrofit Kit)



Trim

**P10170 RT-4RL9-BK**  
(Recessed Trim 4"RL9W-Black)



**P10171 RT-4RL9-CH**  
(Recessed Trim 4"RL9W-Chrome)



**P10173 RT-6RL15-BK**  
(Recessed Trim 6"RL15W-Black)

**P10174 RT-6RL15-CH**  
(Recessed Trim 6"RL15W-Chrome)

**P10172 RT-4RL9-CH-WH**  
(Recessed Trim 4"RL9W-Chrome/White)



**P10176 RTS-4RL9-WH**  
(Recessed Trim 4"RL9W-Square White)




**P10175 RT-6RL15-CH-WH**  
(Recessed Trim 6"RL15W-Chrome/White)

**P10177 RTS-6RL15-WH**  
(Recessed Trim 6"RL15W-Square White)

Photometric Data

4RL - 9W




Zonal Lumen Summary

Zone	Lumens	% Luminaire
0-30	231.72	37.30
0-40	365.01	58.80
0-60	569.33	91.70
60-80	51.56	8.30
70-80	8.79	1.40
90-120	0.00	0.00
90-180	0.00	0.00
0-180	620.89	100.00

Total Luminaire Efficiency = 100.00%



6RL - 15W



Zonal Lumen Summary

Zone	Lumens	% Luminaire
0-30	377.56	36.70
0-40	596.76	58.10
0-60	940.85	91.60
60-80	86.70	8.40
70-80	14.53	1.40
90-120	0.00	0.00
90-180	0.04	0.00
0-180	1027.61	100.00

Total Luminaire Efficiency = 100.00%


Distance	Illuminance at a Distance	
	Center Beam fc	Beam Width
1.7ft	205 fc	3.2 ft x 3.1 ft
3.3ft	54.3 fc	6.2 ft x 6.0 ft
5.0ft	23.7 fc	9.4 ft x 9.2 ft
6.7ft	13.2 fc	12.6 ft x 12.3 ft
8.3ft	8.59 fc	15.7 ft x 15.2 ft
10.0ft	5.92 fc	18.9 ft x 18.3 ft

■ Vert. Spread: 86.7°  
■ Horiz. Spread: 85.0°

Product Dimension


4-inch

Weight: 0.93-lbs




5/6-inch

Weight: 1.19-lbs



Package


4-inch



Package (Master)

20

5/6-inch



Package (Master)

10