

CTP2818BN

City Park Pendant
Brushed Nickel

QUOIZEL
LIGHTING



DETAILS

Material: Steel-Glass

Glass/Shade Description: Seedy Glass

LAMPING

Light Source: Incandescent

Bulb Included: No

Bulb Type: Candelabra Base

Bulb Quantity: 3

Watts per Bulb: 60

ELECTRICAL

Dimmable: Yes

Voltage: 120v

Wire Length: 8'

INSTALLATION

Location Rating: Damp

Install Position: N/A

Sloped Ceiling Compatible: Yes

DIMENSIONS

Dimensions: 17.75" W x 13.5" H x 17.75" D

Overall Height: 50"

Canopy Dimensions: 5.00" Dia.

Chain/Downrod Length: 2 (0.5"D x 6") and 2 (0.5"D x 12")
Down Rods

Weight: 5.00 lbs

Dimensional Weight: 37.00 lbs.

