



Sunlite 28 Watt T5 High Performance Straight Tube, Mini Bi-Pin Base, Super White

- 28-Watt
- 5000K Color Temperature
- 20,000 hour average lamp life



General Characteristics

Bulb
Lamp Type
Lamp Life Hours
Base
Lumens Per Watt (LPW)
Life (based on 3hr/day)
Estimated Energy Cost

T5
 T5 High Performance Straight Tube
 20,000 Hours
 Miniature Bi-Pin (G5)
 89.29
 18.3 Years
 \$3.37 per Year

Electrical Characteristics

Watts

28

Light Characteristics

Brightness
Color Accuracy (CRI)
Light Appearance
Color Temperature

2500 Lumens
 82
 Super White
 5000K

Product Dimensions

MOL (in)
Diameter (in)
Item Dimensions (in)

45.80"
 0.625"
 (W) 0.63 (H) 0.63 (D) 45.80

Product Data

Item Number
Case Quantity
Barcode on SKU
Barcode on Case
Brand
Description

30342-SU
 40
 653703303420
 10653703303427
 SUNLITE
 F28T5/850