



# T&B®

## Armored Cable/Flexible Metal Conduit Fittings T&B Catalog Number:

**UPC Number:** 300-TB  
78621000300  
**Status:** Active  
**Description:**

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 3/8 Inch, Knockout Size 1/2 Inch, Cable Range 0.470 to 0.660 Inch, Steel with Zinc Plating

### Features

Easy to install with double grip saddle, connectors are completely salvageable.

### Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

### General

Trade Size (inches)	3/8
Material	Steel
Finish	Electro Zinc Plated

### Dimension Information

Dimension A (inches)	1 1/4
Dimension B (inches)	1 5/16
Dimension C (inches)	7/16
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.47
Cable Opening-Maximum (inches)	0.66

### Specifications

3dmodel Available on Website

### Packaging

T&B Inner Pack	100
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	6.88 lbs. per 100

### Notes

UL Listed for armored cable and metal clad cable.  
UL listed for new interlocked armor ground type metal clad cable (MCI-A)

### Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E1383

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)