



# S8946

100W/LED/HID/TEMP/5000K/120V  
 100 watt - LED Hi-lumen temporary hi-bay caged lamp; 5000K;  
 Integrated cord / plug and hook; 120 volts



### Features

- For use in any commercial work area
- Includes 36" power cord / plug and hook
- Base up, down, or horizontal operation

S8946

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent		
S8946	Hi-Pro	045923089466	120	100	500W	105W	400W		
Lamp Code			Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
100W/LED/HID/TEMP/5000K/120V			Non-Dimmable	13-1/2"	6-3/4"	12000	50000	5000	Natural Light
CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status	DLC ID:		RoHS Compliant	
85	300	-29C (-20F) to a maximum of +60C (+140F)	4	Box	Lawful for sale in California	PLGCOD3T0H7Q <a href="#">DLC Search</a>		Yes	
UL or ETL Listed			UL Classification			Warranty			
Yes			cULus Classified - Damp Location Rated			<a href="#">5 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

