

LED LAMP

SPECIFICATIONS

Ideal For

Chandeliers | Lanterns

Soft White
2700K

Features

- Instant On To Full Brightness
- Suitable For Damp Locations
- Dimmable
- UL/CUL Listed
- FCC Compliant
- RoHS Compliant
- 100% Mercury Free
- 2 Year Warranty
- Soft White
- Energy Star®

Benefits

- Full Range Dimming
- Energy Efficient: Up to 91% less energy than standard incandescent
- No Ultraviolet - Safe for artwork
- Color Consistency
- Low Heat
- Durable
- Long Life



Specifications

Item Number	Input Power (Watts)	Incandescent Equiv. (Watts)	Input Line Voltage
BPCTC40/827/LED/2	3.8	40	120
Base Type	Lumens	Lumen Efficiency (LPW)	CCT
Candelabra	300	78	2700K
CRI	Beam Angle	MOL	Diameter
>80	N/A	3.85"	1.35"
Life Hours	Minimum Starting Temperature		
15,000	-13°F		