



PRODUCT DESCRIPTION:

Geometric metal frames finished in Black support panes of clear Seedy glass, provides for a refined restoration look. Add vintage bulbs (not included) to complete the authentic feel of this design.

FINISHES OPTION:

Black BK



GLASS:

Seedy CD

MATERIAL:


Steel

CERTIFICATION:

Dry Location

ADDITIONAL:

MB Incandescent (NOT INCLUDED)
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)



MEASUREMENTS:

<u>Length</u>	<u>Width</u>	<u>Height</u>
15.75"	15.75"	9.00"
<u>BP Width</u>	<u>BP Height</u>	
15.75"	1.00"	
<u>Hanging Weight</u>		
13.20 lb		

LAMPING:

2.00 of Bulbs
 60W
 120 TOTAL WATTAGE
 0 RATED LUMENS
 INPUT VOLTAGE: 120

DIMMABLE : Standard Dimmer

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
EASTERN DISTRIBUTION CENTER
 4200 SHIRLEY DR. | ATLANTA, GA 30336
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com