



T&B[®]

Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

UPC Number: 2710
78621002710
Status: Active
Description:

Liquidtight Cord Connector, 2 Inch, Straight, Cord Range 1.850 to 2.190 Inch, Meets Coast Guard CG293, Nylon, Black

Features

Hand tightens, no tools needed for assembly.
Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.

Application

To connect flexible cord to a box or enclosure and provide adequate strain relief.
Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)
Meets Coast Guard CG293

General

Material Nylon

Dimension Information

Hub Size (inches)	2
Dimension A (inches)	4.9
Dimension B (inches)	3.50
Dimension C (inches)	0.84
Cord Range (inches)	1.850-2.190
Throat Diameter (inches)	1.89

Specifications

3dmodel	Available on Website
Temperature Rating	34 C - 105 C

Packaging

Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	66.5 lbs. per 100

Application Support

T&B Instruction Sheets	ta01320-tb2
Product Overview	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com