



# T&B<sup>®</sup>

## Liquidtight Flexible Metal Conduit Fittings T&B Catalog Number:

**UPC Number:** 5243  
78621005243  
**Status:** Active  
**Description:**

Liquidtight Conduit Fitting, 45 Degree 3/4 Inch, Non-Insulated Malleable Iron

### Features

Ability to install quickly with low torque effort

### Application

Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

To positively bond conduit to box or enclosure.

### General

Style	Non-Insulated
Trade Size (inches)	3/4
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### Dimension Information

Dimension A (inches)	1 21/32
Dimension B (inches)	2 1/8
Dimension C (inches)	9/16

### Specifications

3dmodel Available on Website

### Accessories & Components

Wiremesh Grips for Liquidtight Fittings WMG-LT3

### Packaging

T&B Inner Pack	10
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	37.5 lbs. per 100

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:  
E 23018

For further technical assistance, please contact us...

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)