

125A SURF MAIN LUG 8CKT 125A 1PH MLO 8/16C 15 IN. BOX
INDOOR LDCNTR MURRAY



General technical data

Configuration of the busbars	125A
Mounting type	Surface
Phase number	1
Suitability for operation	Residential

Electricity

Ampacity	125 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

Switching capacity

Switching capacity current acc. to EN 60898 rated value	22000 A
---	---------

Model

product brandname	Murray
Product sub brand name	Load Centers

Mechanical Design

Number of width units for installation width	8
--	---

Size of the circuit-breaker	ML
Width [in]	1049.048 in
last modified:	02/22/2017